






REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE



NOTES1:

- 1. Rated voltage/current : 300V / 8A
- 2. Withstanding voltage : AC1600V/1Min.
- 3. Torque value : M2 , 1.77Lb.in
- 4. Wire range : 28~16AWG

IEC Standard

1. Pollution degree	2
Overvoltage category	II
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	250V
Rate current(A)	7A


- 2. Torque value : M2 , 0.2N·m
- 3. Wire range : 0.5~1.5mm<sup>2</sup>

NOTES2:

- 1. Dimension shall be interpreted per ASME Y14.5-2009
- 2. Pitch : 3.5/3.81mm, Poles : N=02~24P
- 3. Stripping length : 6~7mm
- 4. Operating temperature: -40°C~+105°C
- 5. Undimensioned tolerances:

Pitch	range		In	Nominal dimension		range	Tolerance
	mm	Over		mm	Over		
6	TO	10	TO	30	60	100	0.1/10
10	TO	10	TO	60	100	150	≤
24	TO	24	TO	100	150	150	±2
±0.15 ±0.20 ±0.30 ±0.50 ±0.70 ±1.00 ±1.30							

6. RoHS Compliance



- 1. (Grey)
- 2. (Blue)
- 3. (Black)
- 4. (Green)
- 5. (Orange)
- 6. (Red)
- 7. (Transparent)
- 8. (Yellow)
- 9. (White)

DETACHED LISTS			
PART NO.:	/	NAME:	DEGSON® NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司
APPD.:	/	CHKD.:	/
DRFT.:	/	TITLE:	CUSTOMER DRAWING
THIRD ANGLE PROJECTION		DRAWING NO.:	/
		DO NOT SCALE DRAWING	SCALE
			1:1