



CONNECTOR, FEMALE, 2-PIN, 24 V DC FOR SIMATIC HMI PANELS, EXCEPT KEY PANELS, WIRE CROSS-SECTION MM2 UP TO 0.75 AMOUNT: SEE TECHNICAL DATA

Product type designation	
Installation type/mounting	
Wall mounting/direct mounting possible	Yes; can be plugged into SIMATIC HMI device
Supply voltage	
Rated value (DC)	24 V; DC
Interfaces	
Number of pins HMI-side	2; Female
Number of pins device-side	2; Female, screw terminals
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	70 °C
Relative humidity	
• Operation, max.	95 %
Mechanics/material	
Screw type	
• 4.5 V	Yes

Type of housing (front) • plastic	Yes
Dimensions	
Width	10 mm
Height	15 mm
Thickness	27 mm
Scope of supply	
Delivery unit in items	10
other	
Note:	for SIMATIC HMI Panels, except for Key Panel
Usable in the following products	
• Product 1	6AV2124-2DC01-0AX0
• Product 2	6av2124-1*
• Product 3	6av2124-0*
• Product 4	6AV6645-0*
• Product 5	6AV6545-4*
• Product 6	6AV6545-8*
• Product 7	6AV6647-0*
• Product 8	6AV2123-2*
last modified:	12.03.2015