


ROLINE UTP Cable Cat.6 / Class E, Stranded, 300 m

Product No.	21.15.0992
Manufacturer	ROLINE
Manufacturer No.	21.15.0992
EAN (single piece)	7611990110346



Cat.6

- Structured building wiring
- Impedance: 100 Ohm
- Colour: Grey
- Construction: 8 lines, copper, stranded wire AWG23

For a structured cabling system we recommend to use the following components:

- ROLINE Cat.6 UTP Cable, Solid Wire, AWG23: 21.15.0990 (100 m), 21.15.0991 (300 m)
- ROLINE Cat.6 Flush Mount Wall Jack, unshielded: 25.16.8494 (white), 25.16.8500 (ivory)
- ROLINE Cat.6 Surface Mount Wall Jack, unshielded: 25.16.8394 (white), 25.16.8395 (ivory)
- ROLINE Cat.6 19" Patch Panel, 24 Ports, unshielded: 26.11.0355 (light grey), 26.11.0362 (black)
- ROLINE Cat.6 UTP Patch Cord, grey, 5 m: 21.15.0935

The accredited German laboratory GHMT has tested and certified this product combination, in a Channel of 100 meters, as being compliant to Class E specifications; certificate no. z2329b-10-E (with flush mount)/z2330b-10-E (with surface mount).

Technical specifications	
Manufacturer	ROLINE

Product group	Twisted Pair Cable
Product type	installation cable
Colour	grey
Length	300 m
Shield type	UTP
Transfer quality	Cat6 / Class E
Impedance	100 Ohm
Quantity of wires	8
Conductor cross section (AWG)	AWG 24
Conductor type	Wire
Cable LSOH	No
Material (external cable mantle)	PVC