



# Power Supplies

## transformers



### DOUBLE BOBIN ISOLATED TRANSFORMER

Finest quality construction. Type tested to 4kV primary to secondary. All primary windings rated at 220/240 V AC. Suitable for use with domestic electrical equipment. Double insulated primary windings.

Power Input . . . . . 220-240 V AC @ 50 Hz


### HIGH QUALITY TOROIDAL TRANSFORMER

High quality toroidal transformers. Type tested to 4k V. High power density for size, low magnetic interference. All primary windings rated at 220/240 V AC. Supplied with fixing kit.

Power Input . . . . . 220-240 V AC @ 50 Hz

| Ref No. | Outputs (V AC) | Power (W) | Dimensions (mm) |
|---------|----------------|-----------|-----------------|
| P042A   | 0-12,0-12      | 30        | 70x70x30        |
| P042B   | 0-6,0-6        | 50        | 80x80x30        |
| P042C   | 0-12, 0-12     | 50        | 80x80x30        |
| P042D   | 0-12,0-12      | 80        | 80x80x40        |
| P042E   | 0-22,0-22      | 80        | 80x80x40        |
| P042F   | 0-12,0-12      | 120       | 95x95x40        |
| P042G   | 0-30,0-30      | 120       | 95x95x40        |
| P042H   | 0-110,0-110    | 120       | 95x95x40        |
| P042J   | 0-12,0-12      | 160       | 95x95x55        |
| P042K   | 0-35,0-35      | 160       | 95x95x55        |
| P042L   | 0-12,0-12      | 225       | 105x105x55      |
| P042M   | 0-35,0-35      | 225       | 105x105x55      |
| P042N   | 0-110,0-110    | 225       | 105x105x55      |
| P042P   | 0-12,0-12      | 300       | 110x110x55      |
| P042Q   | 0-35,0-35      | 300       | 110x110x55      |
| P042S   | 0-35,0-35      | 500       | 120x120x65      |

| Ref No. | Outputs (V AC) | Power (W) | Type             | Dimensions (mm) |
|---------|----------------|-----------|------------------|-----------------|
| P014A   | 6-0-6          | 1.2       | 100 mA Secondary | 31x36x30        |
| P015    | 6-0-6          | 3         | 250 mA Secondary | 43x35x34        |
| P017A   | 9-0-9          | 1.8       | 100 mA Secondary | 36x31x30        |
| P018    | 9-0-9          | 4.5       | 250 mA Secondary | 43x35x35        |
| P020A   | 12-0-12        | 2.4       | 100 mA Secondary | 36x31x33        |
| P021    | 12-0-12        | 6         | 250 mA Secondary | 43x35x36        |
| P021A   | 0-12/0-12      | 12        | 500 mA Secondary | 56x47x43        |
| P025    | 9-0-9          | 18        | 1 A Secondary    | 50x42x41        |
| P027    | 12-0-12        | 24        | 1 A Secondary    | 56x47x54        |
| P028    | 15-0-15        | 30        | 1 A Secondary    | 59x50x54        |
| P029A   | 6-0-6          | 24        | 2 A Secondary    | 59x50x54        |
| P031    | 6-0-6          | 18        | 1.5 A Secondary  | 50x42x43        |
| P034    | 9-0-9          | 36        | 2 A Secondary    | 59x50x59        |
| P034A   | 12-0-12        | 48        | 2 A Secondary    | 68x57x55        |
| P034B   | 0-12/0-12      | 48        | 2 A Secondary    | 68x57x55        |
| P037    | 30-0-30        | 120       | 2 A Secondary    | 78x65x66        |
| P037A   | 0-15           | 45        | 3 A Secondary    | 68x58x62        |
| P037C   | 6-0-6          | 48        | 4 A Secondary    | 68x57x54        |
| P037D   | 6-0-6          | 96        | 8 A Secondary    | 78x65x72        |
| P037F   | 9-0-9          | 72        | 4 A Secondary    | 68x57x42        |
| P037G   | 12-0-12        | 72        | 3 A Secondary    | 68x57x70        |
| P037GA  | 18             | 180       | 10 A Secondary   | 75x60x70        |




### INPUT DRIVER TRANSFORMER

A good quality driver transformer for use with audio circuits.

Dimensions (mm) . . . . . 16x20x16

| Ref No. | Outputs (Ohms) | Inputs (Ohms) |
|---------|----------------|---------------|
| P631M   | 2 @ 1k         | 20k           |
| P631T   | 2 @ 3.2        | 1.2k          |



### 100V LINE TRANSFORMER

Converts 100 Volt line signal to 8 or 16 Ohm.

Outputs . . . . . 8 & 16 Ohm

| Ref No. | Dimensions (mm) | Fixing Centres | Tappings (W)       |
|---------|-----------------|----------------|--------------------|
| P037S   | 44x37x35        | 50             | 0.5,1,2,4          |
| P037T   | 50x42x40        | 60             | 1,2,4,8            |
| P634T   | 35x16x35        | 50             | 0.6,1,25,2.5,5,10  |
| P038    | 50x42x40        | 60             | 1.25,2.5,5,10,15   |
| P037U   | 50x42x40        | 60             | 4,8,12,16          |
| P635    | 47x77x40        | 67             | 2.5,5,10,15,20     |
| P635F   | 48x75x45        | 65             | 1.9,3.75,7.5,15,30 |
| P038A   | 56x47x43        | 69             | 10,20,30,40        |



### P036DC

### 50 VA LIGHTING TRANSFORMER

Finest quality construction. Type tested to 4 kV primary to secondary. All primary windings rated at 220/240 V AC. Suitable for use with domestic electrical equipment.

Dimensions (mm) . . . . . 67x60x56

Power Input . . . . . 230 V AC @ 50 Hz

Outputs . . . . . 12 V AC

Power (VA) . . . . . 50