

## Hinges • long version

### 25165.0065



#### Product Description

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

#### Material


##### Body

- Stainless steel 1.4301

##### Axis

- Stainless steel 1.4301


#### Drawing



picture 1

picture 2

picture 3



## Order information

| Dimensions                                 |                |                |                |                | Holding force  |                |                |  | Art. No.   |
|--------------------------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-------------------------------------------------------------------------------------|------------|
| b <sub>1</sub>                             | l <sub>1</sub> | d <sub>2</sub> | h <sub>1</sub> | h <sub>2</sub> | F <sub>1</sub> | F <sub>2</sub> | F <sub>3</sub> |                                                                                     |            |
| [mm]                                       |                |                |                |                | ~              | ~              | ~              |                                                                                     |            |
| without bores – picture 1, Stainless steel |                |                |                |                |                |                |                |                                                                                     |            |
| 60                                         | 90             | 6              | 10             | 2              | 3000           | 3000           | 1200           | 127                                                                                 | 25165.0065 |

## Compliance

## RoHS-compliant

Compliant with Directive 2011/65/EU [RoHS].

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 25.06.2025.

## SCIP-code

N/A

## Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

## Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

## POP-compliant

Contains no persistent organic pollutants – Stockholm Convention [POP] as of September 2025.

## PFAS-compliant

Contains no per- and polyfluoroalkyl substances (PFAS).

## TSCA-compliant

Agent concentration in this product does not exceed the specified threshold.