

Product information

97 52 30

KNIPEX PreciForce®

Crimping Pliers



- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatiguereduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened

General	
Article No.	97 52 30
EAN	4003773051855
Pliers	burnished
Handles	with multi-component grips
Weight	477 g
Dimensions	220 x 70 x 31 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details	
Application	non-insulated crimp connectors in accordance with DIN 46267
Capacity in square millimetres	1.5 — 10.0 mm²
Number of crimping positions	5
AWG	16 — 12

technical change and errors excepted