

Digital inspection camera

micro CA-150™

RIDGID

Application:

For detailed visual inspections in hard-to-reach spots.

Execution:

- 3.5" colour LCD display with 320 x 240 pixel resolution
- aluminium camera head with ultra-bright LED illumination
- Flexible camera cable (waterproof camera head and cable)
- Internal memory of up to 20 images

Advantage:

- Camera cable extendable up to 9 m using extensions
- live images transmitted to external device via video output
- Digital 4x 90° screen rotation for upright image display



Art. no.	41500 050
Brand	RIDGID
Manufacturer Part Number	36848
Image rotation	360° (4 x 90°)
Display resolution	320 x 240 pix
Model	micro CA-150
Field of vision	72 Degree
Screen size	3.5 in
Internal memory	No
External memory on SD card	No
Camera head diameter	17 mm
Number of LEDs	4 PCS
Cable length	0.9 m
Camera cable, extending	Yes
Speech recording	No
Image, video and audio recording	No
Video output	PAL, NTSC
Number of rechargeable batteries/batteries	4 PCS
Battery designation	Mignon AA, LR6, R6, UM3
Gross Weight	2.396 kg
Product Group	412

EAN

0095691368485