

Multi-purpose ladder

3 pieces



Version:

- Rails made of extruded aluminium profiles for optimum stability
- step-strut connections made of high-strength, high-quality flanging
- solid connection
- top section can be used separately as a leaning ladder for rungs 3x6 to 3x10
- High-strength Perlon straps with sewn-in fixing clip prevent splay
- construction around the strut for optimum connection of the guide fittings
- fitting type means lifting protection and guide fittings are interchangeable
- Replaceable plastic shoes for skid-resistant footing
- can be used on stairs for 3 x 6 and 3 x 10

Art. no.	50260 500
Number of rungs	3 x 14
Min./max. length as standard ladder	4.15-9.7 m
Max. working height as standard ladder	10.4 m
Length stabiliser bar	1.2 m
Weight	36.4 kg
Accessibility	Both sides
Material	Aluminium
Folding	Yes
EN standard	131



EAN-Code

4003866415441