

## Bolt end cutters



### Application:


For cutting bolts, tie rods and steel wire.

### Execution:

- Blade: Chrome-vanadium heavy-duty steel, forged, oil-hardened
- Joint: Special tool steel, forged
- Pivot arms: Steel pipe, powder-coated
- Grey-atramentised top

### Advantage:

- Forged stop with comfortable damper
- Extremely flat top and joint area ensure excellent accessibility
- Pivot arm at ergonomic angle for fatigue-free working
- Robust and excellent non-slip two-component handles
- Precise adjustments (12x) and re-adjustments using eccentric screws



|  |                     |
|--|---------------------|
| <b>Art. no.</b>                                  | <b>53273 030</b>    |
| <b>Brand</b>                                     | KNIPEX              |
| <b>Manufacturer Part Number</b>                  | 71 72 760           |
| <b>Length</b>                                    | 760 mm              |
| <b>Max. piano wire diameter cutting capacity</b> | 8 mm                |
| <b>Max. soft wire diameter cutting capacity</b>  | 11 mm               |
| <b>Material of handle</b>                        | 2-component plastic |
| <b>Gross Weight</b>                              | 4.285 kg            |
| <b>Product Group</b>                             | 535                 |

### EAN

4003773066774