



Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
—	03					

PRODUCT CODE DESCRIPTION

IT18R\_UV  
 COLOR  
 (CONSULT FACTORY FOR AVAILABLE COLORS)



Aerospace Spec SAE AS33681-5E	Product Code	Cable Range (mm)	Material	A	B	D	E	G	H	J	K	Min Loop Tensile Strength (newtons)
yes	IT18R_	4.8 to 19	PA66	1.0 ±0.2	2.4±0.2	3.8 ±0.5	4.5 ±0.5	100.0 ±5.0	7.0 ±0.5	25.0 ±0.5	8.0 ±0.5	80
yes	IT18R_UV		PA66UV									
no	IT18R_VO		PA66VO									

SEE CHART

Material


Dimension tolerances  
unless otherwise specified

- .XXXX = ± .0130
- .XXX = ± .130
- .XX = ± .30
- .X = ± .8
- ∠ = ± 0.5 °

Dimension Units mm

PERFORMANCE  
SPECIFICATION

ACAD  
2004



ALL PROPRIETARY RIGHTS IN THE  
SUBJECT MATTER SHOWN ON THIS  
DRAWING ARE EXCLUSIVE  
PROPERTY OF HELLERMANN TYTON

Drawn G. GEIGER 10/9/91  
Approved K.A.C. 07/29/03

**HellermannTyton**

7930 N. Faulkner Rd.  
Milwaukee, WI 53224  
Ph: (414) 355-1130  
Fx: (414) 362-8338

Scale 2:1  
Computer File Number CT\CST\2018006\_03  
Title

**IT18R  
IDENTIFICATION TIE**

Drawing-No

**CT2018006CST**

Format  
AH  
Sheet 1 of 1