




USB A type, 3.0 Female Connector modular

Item No. 2001C201



mm±0.2



PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	STDA_SSRX-
6	STDA_SSRX+
7	GND_DRAIN
8	STDA_SSTX-
9	STDA_SSTX+
Shell	Shield



Screwdriver Included



Material:
 Housing: PP
 Insulator: LCP
 Connector shell: SPCC with plated Ni 40µ min.
 Contact: Brass with plated Au3µ
 Technical:
 Voltage rating: 30V max.
 Current rating: 1.5A max.
 Contact resistance: 30mΩ max.
 Insulation resistance: 1000MΩ min.
 Dielectric withstanding voltage: 500V/AC(R.M.S)
 Operation temperature: -20 ~85°C