



MANA BASE WL PHASE

**Wall-mounted light anthracite round 15W 800/820lm
2700/3000K CRI90 Dimmable**

The MANA BASE WL PHASE wall light is dimmable and designed with a high-performance LED, which allows configuration of the colour temperature before installation (2700/3000K). Thanks to its IP65 protection class rating, this aluminium and polycarbonate (PC) outdoor light is protected in any weather. With a CRI of over 90, colours have a natural appearance. It is quick and easy to establish a direct connection to a 220 volt supply. Please note, the MANA BASE WL PHASE must be combined with the matching MANA shade.

TECHNICAL DATA

Item no.	1006319
IP Code	IP 65
Assembly	Surface
Assembly details	Wall
Dimmable	Yes
Dimming technology	trailing edge
Number of through-wires	68
Primary nominal voltage	220-240V ~50/60Hz
Secondary power / voltage	350 mA
Safety class	I
Wattage	15 W
Minimum ambient temperature	-20 °C
Maximum ambient temperature	40 °C
Level of inrush current	14 A
Duration of inrush current	8.5 µs
Stroboscopic effect (SVM)	0.1
Lumen	800 / 820 lm
Colour temperature	2700/3000 Kelvin
Color	anthracite
CRI	90
LXXBXX data	L80B50
Service life	50000 h

Light Source

916354		Risk Group	1
		Height	9 cm
		Diameter	10 cm
		Net weight	0.5 kg
		Gross weight	0.535 kg