



## POWER ADAPTER W65ACC GaN

Fast Charger

(Intenso)<sup>®</sup>  
for everyday life

**QUALITY AUDIT**  
Tested in Germany ✓

### Technische Informationen

Colour:	white
Surface:	plastic
Input connector:	EU connector
Input voltage:	100 - 240 V
Input alternating current frequency:	50 / 60 Hz
Connections:	USB-C 1, USB-C2, USB-A
Average efficiency:	91.43%
Efficiency at low load (10%):	84.46%
Power consumption at no load:	0.26 W
Dimensions:	44.4 x 29.4 x 91.22 mm
Weight:	143.4 g

### What is GaN?



GaN adapters are a new type of power adapter that have many advantages compared to conventional, silicon-based adapters. GaN stands for Gallium Nitride, a material with a higher power density and efficiency. The use of GaN enables smaller power adapters that can also handle higher voltages and currents and even produce less heat.

This makes our power adapters with GaN technology **smaller, faster** and above all, more **energy efficient!**

### Product data

Colour	Article no	EAN	Packing unit
white	7806512	4 034303 033379	2pcs

Output: supports (downwards compatible)  
PD 3.0, PPS and QC 4.0

USB-C 1/2: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 15.0 V/DC 3.0 A, max. 45.0 W 20.0 V/DC 3.25 A, max. 65.0 W PPS: 3.3 – 11.0 V/DC 5.0 A, max. 55.0 W USB-A: 4.5 V/DC 5.0 A, max. 22.5 W 5.0 V/DC 4.5 A, max. 22.5 W 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 20.0 V/DC 3.0 A, max. 60.0 W USB-C 1 + USB-C 2 + USB-A: USB-C 1: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 15.0 V/DC 3.0 A, max. 45.0 W 20.0 V/DC 2.25 A, max. 45.0 W USB-C 2 + USB-A: 5.0 V/DC 3.0 A, max. 15.0 W (shared) Total: max. 60.0 W	USB-C 1 + USB-C 2: USB-C 1: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 15.0 V/DC 3.0 A, max. 45.0 W 20.0 V/DC 2.25 A, max. 45.0 W USB-C 2: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 2.22 A, max. 20.0 W 12.0 V/DC 1.67 A, max. 20.0 W Total: max. 65.0 W USB-C 1 + USB-A: USB-C 1: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 15.0 V/DC 3.0 A, max. 45.0 W 20.0 V/DC 2.25 A, max. 45.0 W USB-A: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 2.0 A, max. 18.0 W 12.0 V/DC 1.5 A, max. 18.0 W Total: max. 63.0 W USB-C 2 + USB-A: 5.0 V/DC 3.0 A, max. 15.0 W Total: max. 15.0 W (shared)
---	--