

**ANRITSU METER**

Home / Temperature probes / Model MG

- Instruments
- Temperature probes
- Company info
- Contact
- Site map

[Application / Technical guide / Request catalogue](#)

[sales@anritsu-meter.co.jp](mailto:sales@anritsu-meter.co.jp)

**Model MG series**  
Magnet Temperature Probes


Model MG series is for magnetic surface of temperature measurement. The magnetic force of MG-11 is bigger than MG-21.

**Typical Probes of MG series**

Model **MG-11K-TS1-ANP**




Model **MG-22K-GW1-ANP**



Max.Temp.	Accuracy	Response time	Durability
250°C	±1.3°C (100°C Surface)	2.0s	A

Max.Temp.	Accuracy	Response time	Durability
400°C	±1.4°C (100°C Surface)	2.0s	A




Specifications	
Accuracy	Standard type ±1.3°C Miniature type ±1.4°C
Response time	2.0s
Durability	A
Max.Temp.	Low temp. 250°C High temp. 400°C

**MG-11K-TS1-ANP**  
1 2 3 4 5 6

How to order

1.Head size	-1	Standard type
	-2	Miniature type
2.Guard Material	1	Max Temp. 250°C
	2	Max Temp. 400°C
3.Thermocouple	K	Chromel-Alumel
	E	Chromel-Constantan
4.Cable type	-TS	For WE-*1
	-GW	For WE-*2
5.Cable length	1	1m
	1.5	1.5m
	2	2m
	2.5	2.5m
	--	-----
6.plug	-ANP	P plug
	-W	Without plug

1.Head size  
You can choice Head size as below.



2.Guard Material  
You can choice Guard Material as below.

