

Within Series Adaptor 31_BNC-50-0-1/133_N

Description

Adaptor jack/jack
BNC jack (female) / BNC jack (female)

Interface standard
Series BNC - IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz
VSWR	DC - 4 GHz ≤ 1.06 + 0.04 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0123 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS)	-65 °C to 165 °C compliant
--	-------------------------------

Material Data

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00013802
-------------------	--------------

Ordering Information

Single package	31_BNC-50-0-1/133_NE
----------------	----------------------