

FEATURES

- Good flexibility for ease of use
- Resistant to a wide range of chemicals including many acids / alkalis
- Specially selected high tensile polyester fibres
- EC compliant for food contact applications
- Manufactured from cadmium and silicone-free materials
- Using a specialist PVC that can reduce the taint of drinking water

RS PRO PVC Flexible Tubing, Transparent, 18.5mm External Diameter, 25m LongReinforced, 55mm Bend Radius, Applications

RS Stock No.: 440-880



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Flexible Tubes



Product Description

This RS Pro PVC tubing is perfect to use in a multitude of applications, whether is DIY or commercial use, the EC compliant low toxic hose is reliable and highly durable over time. Suitable for liquids such as water, fuels, oils and other chemicals, this RS Pro hose is also suited for use within the food industry and can be used for air and gas applications. This multi-purpose, high-qualityall-round performer is universally popular, especially for the conveyance of air and water.

General Specifications

Material	PVC
Colour	Transparent
Reinforced	Yes
Application	Chemical, Compressed Air, Food, Liquid, Water, Widely used by the caravan industry for piping water and chemicals, Popular for pharmaceutical / scientific applications for the transfer of chemicals, Air applications such as pneumatic tools, For the transfer of food substances and liquids

Mechanical Specifications

Inner Diameter	12.5mm
Outer Diameter	18.5mm
Length	25m
Bend Radius	55mm
Safety Factor	4:1



Operation Environment Specifications

Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Maximum Working Pressure	15 bar

Approvals

Compliance/Certifications	BS6066, ISO5774/ RoHS compliant



roduc	t Rof	CR03	CR05	CR06	CR08	CR10	CR12	
X	30m roll	,			***			
tock	100m roll		7					
Vomina	size	3.0 x 8mm	5 x 10mm	6.3 x 11.5mm	8 x 13.5mm	10 x 16mm	12.5 x 18.5mm	
nternal	Diameter	3.2 ± 0.20mm	4.75mm ± 0.25	6.3 ± 0.25mm	8.0 ± 0.25mm	10.0 ± 0.25mm	12.5 ± 0.25mm	
xtema	Diameter	8.0 ± 0.25mm	10.0mm ± 0.25	11.5 ± 0.30mm	13.5 ± 0.30mm	16.0± 0.30mm	18.5 ± 0.30mm	
ength 1	Tolerance			BS EN I	SO 1307 (± 1%)			
Maximu Pressur	m Working e	32 Bar	27 Bar	16 Bar	16 Bar	15 Bar	15 Bar	
Vinimur Pressur	n Burst e	128 Bar	108 Bar	64 Bar	64 Bar	60 Bar	60 Bar	
lend ra	dius	20mm	20mm	28mm	29mm	40mm	55mm	
Varking emper				- 15	°C to + 60°C			
/aterial		Flexible PVC						
Vaterial	Softness	BSS45 FDA Approved						
lamma	-				Extinguishing			
Weight (per meter	0.066Kg	0.074Kg	0.093Kg	0.123Kg	0.163Kg	0.187Kg	
Coil We	ight	1.68 Kg	2.22Kg	2.78Kg	3.70Kg	4.89Kg	5.61Kg	
ackagi	ng	Strapex Ties and Shrinkwrap						
Applical Standar		BS EN ISO 5774 (Plastic hoses. Textile-reinforced types for compressed-air applications.) & BS EN ISO 6224 (Thermoplastics hoses, textile reinforced, for general- purpose water applications)						

Flexible Tubes



Product Ref		CR16	CR19	CR25	CR32	CR38	CR50
x	30m roll					0.	
Stock	100m roll						
Vomina	size	16 x 23mm	19 x 26mm	25 x 33mm	32 x 42mm	38 x 48mm	50 x 62mm
nternal	Diameter	16.0 ± 0.25mm	19.0 ± 0.25mm	25.0 ± 0.50mm	32.0 ± 0.50mm	38.0 ± 0.50mm	50.0 ± 0.75mm
xterna	Diameter	23.0 ± 0.50mm	25.75 ± 0.50mm	32.50 ± 0.50mm	42.0 ± 0.75mm	48.0 ± 1.00mm	62.0 ± 1.00mm
	Tolerance						
Maximu Pressur	m Working 9	12 Bar	10 Bar	10 Bar	10 Bar	10 Bar	8 Bar
Minimur Pressur	n Burst 9	48 Bar	40 Bar	40 Bar	40 Bar	40 Bar	32 Bar
end ra	dius	95mm	135mm	210mm	320mm	420mm	650mm
Working Temper							
/ateria							
-	Softness						
lamma							
	per meter	0.269Kg	0.310Kg	0.432Kg	0.684Kg	0.684Kg	1.476Kg
Coil We		8.00Kg	9.30Kg	12.96Kg	20.52Kg	20.52Kg	44.29
Packag	-	97400091001					
Applical Standar							