



24-Port Gigabit Smart Managed Pro Switch with PoE+ and 2 SFP Ports GS724TPv2 Product Setup Sheet

Category

Smart Managed Pro Switches

Product Name

NETGEAR 24-Port Gigabit PoE+ Smart Managed Pro Switch with 2 SFP Ports (GS724TPv2)



Ecom Product Nomenclature

157 characters: NETGEAR 24-Port Gigabit PoE+ Ethernet Smart Managed Pro Switch with 2 SFP Ports |190W |ProSAFE Lifetime warranty and lifetime technical chat support (GS724TPv2)

101 characters: NETGEAR 24-Port 190W Gigabit PoE+ Ethernet Smart Managed Pro Switch with 2 SFP Ports (GS724TPv2)


81 characters: NETGEAR 24-Port Gigabit PoE+ Smart Managed Pro Switch with 2 SFP (GS724TPv2)

67 characters: NETGEAR 24p Gigabit PoE+ Smart Managed Pro Switch (GS724TPv2)

52 characters: NETGEAR 24p Gigabit PoE+ Switch (GS724TPv2)

Package Contents

- Switch
- Power cord(s)
- Rubber footpads for tabletop installation
- Rubber protection caps in SFP sockets
- Screws for rack mounting
- Brackets for rack mounting
- Installation guide
- Resource CD with NETGEAR Smart Control Center utility





24-Port Gigabit Smart Managed Pro Switch with PoE+ and 2 SFP Ports GS724TPv2 Product Setup Sheet

Product Descriptions

15 words

Introducing the NETGEAR GS724TPv2 24-Port Gigabit PoE+ Smart Managed Pro Switch with 190W PoE budget.

25 words

The NETGEAR GS724TPv2 24-Port Gigabit PoE+ Smart Managed Pro Switch offers 190W budget and 2 dedicated SFP ports for wireless converged networks, IP surveillance and mobility.

50 words

The NETGEAR GS724TPv2 24-Port Gigabit PoE+ Smart Managed Pro Switch offers 190W budget and 2 dedicated SFP ports for wireless converged networks, IP surveillance and mobility. Advanced features such Access Control Lists (ACLs), L2/L3/L4 QoS (DiffServ), LACP link aggregation and Spanning Tree will satisfy even the most advanced small business networks.

100 words

The NETGEAR GS724TPv2 24-Port Gigabit Smart Managed Pro Switch comes with 24 PoE+ copper ports and 2 dedicated SFP ports for fiber uplinks. Cautious spender organizations can now deploy denser PoE+ devices with a reasonable PoE power budget of 190W. With temperature-based fan-speed control, the GS724TPv2 supports quiet rack mounting operation with a maximum of 32.4dB at 25°C (77°F) ambient. The GS724TPv2 offers an easy-to-use Web browser-based management GUI with configurable L2 network features like VLANs and PoE operation scheduling, allowing SMB customers to deploy PoE-based VoIP phones and IP surveillance. Advanced features such Access Control Lists (ACLs), L2/L3/L4 QoS (DiffServ), LACP link aggregation and Spanning Tree will satisfy even the most advanced small business networks. The GS724TPv2 features Energy Efficient Ethernet (IEEE 802.3az) for maximum power savings and is backed by NETGEAR ProSAFE Lifetime Limited Warranty and 24/7 support including lifetime chat.

Approved Category/Space Definitions

When referring to the "space" or category, the following is approved for all expected types of usage:

- Smart Managed Pro Switches


NETGEAR®

24-Port Gigabit Smart Managed Pro Switch with PoE+ and 2 SFP Ports GS724TPv2 Product Setup Sheet

Ordering Information

NETGEAR Part Number	UPC Number (GTIN-12)	EAN Number (GTIN-14)	Country
GS724TP-200AJS	606449119220	10606449119227	Asia Pacific region
GS724TP-200EUS	606449119244	10606449119241	Europe region
GS724TP-200INS	606449119251	10606449119258	India
GS724TP-200NAS	606449119268	10606449119265	North America region
GS724TP-200PRS	606449119237	10606449119234	China

Case Pack Qty	3		
Case Weight	kg	lb	
AJS	14.65	32.26	
EUS	14.77	32.54	
INS	14.11	31.07	
NAS	13.99	30.81	
PRS	14.12	31.09	
Case Dimensions	Length	Width	Height
mm	597	304	379
in	23.52	11.98	14.93



Brown Box Weight	kg	lb	
AJS	4.27	9.41	
EUS	4.31	9.50	
INS	4.09	9.01	
NAS	4.05	8.93	
PRS	4.10	9.02	
Brown Box Dimensions	Length	Width	Height
mm	564	318	89
in	22.22	12.53	3.51



Warranty	Lifetime
ECCN	5A992
HTS	8517.62.0050
Country of Origin	China

Product Weight	kg	lb	(Product itself)
	3.15	6.93	
Product Dimensions	Width	Depth	Height
mm	440	204	43
in	17.34	8.04	1.69

