

Pluggable Terminal Blocks

3.81 mm Pitch, female plug



FEATURES:

Polarised mouldings

Withstand Voltage - AC2000V/1min

Guided pin alignment

Tin plated wire protector

SPECIFICATION:

Gender of contacts	Female
Rated current to EN	8 A
Pitch	3.81 mm
Termination type	Screw Connection
Connection direction	vertical
Rated voltage to EN	125 V
Combustibility class	UL 94 V-0
Colour	green
Temperature range	-33...+120 °C
Cross-section max.	1.31 mm ²
Cross-section min.	0.13 mm ²
Connection cross-section	0.13-1.31 mm ² (26-16AWG)



PRODUCT RANGE:

Art. Nr.	Poles	A	Length
RND 205-00122	2	7.6 mm	7.6 mm
RND 205-00123	3	11.43 mm	11.43 mm
RND 205-00124	4	15.24 mm	15.24 mm
RND 205-00125	5	19.05 mm	19.05 mm
RND 205-00126	6	22.86 mm	22.86 mm
RND 205-00128	8	30.48 mm	30.48 mm
RND 205-00129	9	34.29 mm	34.29 mm

