


# E11657



## Wirable socket

SDOGH040MSSFKPG



### Application

Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes

### Electrical data

Operating voltage	[V]	< 45 AC / < 70 DC
Max. current load total	[A]	4; (...40 °C)

### Operating conditions

Ambient temperature	[°C]	-25...100
Protection		IP 68

### Mechanical data

Weight	[g]	28.8
Dimensions	[mm]	18 x 18 x 46
Materials		PA
Material nut		brass, nickel-plated

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

screw terminals: ...0.75 mm<sup>2</sup>; Cable sheath: Ø 6...8 mm


### Electrical connection - socket

Connector: 1 x M12, straight; Moulded body: PA; Locking: brass, nickel-plated; Contacts: gold-plated

# E11657

## Wirable socket

SDOGH040MSSFKPG



### Connection

