

SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE


24...230V LED M16x1.5

Form A (18 mm) for pressure switch
 24...230 V AC/DC
 LED red (2) green (1)
 metric



Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



stay connected



Height: 41 mm

Product may differ from Image

Approvals



Form

29321

Technical Data

Operating voltage	24...230 V AC/DC
LED display	red (2) green (1)
Current consumption	24 V: approx. 40 mA; 110 V: approx. 3 mA; 230 V: approx. 6 mA
Operating current per contact	max. 4 A
Compression gland	M16 × 1.5 mm
Sealing range (cable diameter)	5...10 mm
Plug color	Black housing, transparent flip top
Protection	IP65 inserted and tightened (EN 60529), with gland
Locking of ports	M3 (recommended torque 0.4 Nm)
Connection cross section	4 mm ² single core, with ferrule end 1.5 mm ²

General data

Temperature range	-20...+60 °C
-------------------	--------------

Commercial data

country of origin	CZ
customs tariff number	85366990

minimum order quantity

1