

PCB TERMINAL BLOCKS

5mm Pitch Low Profile 45° Rising Clamp Terminal Blocks

PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS




RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS

- 2 & 3 pole interlocking
- 4-12 pole pre-assembled
- 45° mounting
- Moulded in grey UL94-V0 flame retardant PA
- Professional rising clamp terminals
- 0.2-4.0mm² (30-12AWG) solid cable
- 0.2-2.5mm² (30-12AWG) stranded cable
- Captive screw
-    approved


CTB3000



| TYPE NO. | POLES | LENGTH |
|------------|-------|--------|
| CTB3000/2 | 2 | 10mm |
| CTB3000/3 | 3 | 15mm |
| CTB3000/4 | 4 | 20mm |
| CTB3000/5 | 5 | 25mm |
| CTB3000/6 | 6 | 30mm |
| CTB3000/7 | 7 | 35mm |
| CTB3000/8 | 8 | 40mm |
| CTB3000/9 | 9 | 45mm |
| CTB3000/10 | 10 | 50mm |
| CTB3000/11 | 11 | 55mm |
| CTB3000/12 | 12 | 60mm |

SPECIFICATION

| | |
|---------------------------|---|
| Rating | 24A/160V UL=16A/300V, VDE&IMQ=24A/130V |
| Dielectric strength | ≥1.25kV |
| Impulse withstand voltage | 2.5kV |
| Working temperature | 110°C |
| Moulding | UL94-V0 flame retardant PA |
| Pin/terminal | Tinned, nickel plated brass |
| Rising clamp | Tinned, nickel plated brass |
| Screw/torque | M3 steel zinc plated, 0.5Nm |
| Recommended PCB hole size | ø1.3mm |



CAMDENBOSS

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1.1

+44 (0)1638 716101
info@camdenboss.com
www.camdenboss.com



FM 28614 EMS 613558