




NOTE:

- CABLE: NON-UL, NON-FOIL, 28AWG*4C (RED/YELLOW/GREEN/BLACK) BLACK COLOR, OD=2.6±0.05mm, TPU JACKET.
- LENGTH: 0.3M/0.15M.
- CONNECTORS: TYPE(C) M*1PCS (SHELL NICKEL).
3.5F*2PCS ((SHELL GOLD PLATED)).
- MOLD: MOLDING USB TYPE.
- CONTACTS:

TYPE C	1	2	3	4
3.5 JACKET	1	2	3	64
3.5 JACKET	1	2	3	64
	MIC	L	R	GND
	RED	YW	GR	BK
- OPEN/SHORT TEST: 100% TEST.
A. 100% OPEN, SHORT & INTERMITTANCE TEST.
B. CONDUCTOR RESISTANCE: 3ohms MAX:
C. INSULATION RESISTANCE: 10MΩ/, 10ms:



1PCS/OPP BAG+LABEL

COMPANY	CDL	ITEM NO.	PSG91712	NO	B
REVISION	DATE	DISCRIPTION	DRAWN BY		
REV.A/0	2019.06.25		DESIGNED BY		
			APPROVAL BY		

PRO-SIGNAL

SCALE	NON
UNIT(mm)	
DRAWING NO.	