



#### RE1340-LF

- Epoxy fibre-glass FR4 0.80 mm
- Single-sided 35 µm Cu
- Without holes
- Hot air leveling (HAL-leadfree)
- 10 self-adhesive SO8-Adapters
- Pre-scratched rated break point for the separation of individual modules from the board
- Size 19.00 x 67.25 mm




#### RE1340-LF

- Epoxydglashartgewebe FR4 0,80 mm
- Einseitig 35 µm Cu
- Keine Bohrungen
- Heißverzinkt (HAL-leadfree)
- 10 selbstklebende SO8-Adapter
- Vorgeritzte Sollbruchstellen
- Größe 19,00 x 67,25 mm



#### RE1340-LF

- Fibre de verre époxyde FR4 0,80 mm
- Simple face 35 µm Cu
- Sans trous
- Étamée à chaud (HAL-leadfree)
- 10 adaptateurs SO8 autoadhésifs
- Points destinés à la rupture
- Dimensions 19,00 x 67,25 mm



#### RE1340-LF

- Fibra de vidrio epoxídica FR4 0,80 mm
- Por dos lados 35 µm de Cu
- Sin agujeros
- Estañado en caliente (HAL-leadfree)
- 10 adaptadores autoadhesivos tipo SO8
- Punto de rotura controlada tallado
- Tamaño 19,00 x 67,25 mm