

Product information

38 15 200

- High bending strength of the pliers tips
- Straight, half-round jaws
- Vanadium electric steel; forged, oil-hardened

Mechanics' Pliers

DIN ISO 5745




General

Article No.	38 15 200
EAN	4003773039594
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	209 g
Dimensions	200 x 61 x 13 mm
Standard	DIN ISO 5745
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw thickness (joint) (T1)	9.5 mm
Tips width (W4)	3.0 mm
Tips thickness (T2)	2.5 mm
Jaw length (L3)	73.0 mm
Head width (W3)	17.5 mm



technical change and errors excepted