

**MNX PC 125/75 HG**



Sample photo

**Order symbol:** PC 125/75 HG  
**Product nbr:** 6011308  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074014023  
**EI. number:**  
 Finland: 3420332  
 Electric No. Denmark: 8212022276  
 Electric No. Italy: 7351057  
 Electric No. Sweden: 6011308

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	130	130	75	MIN 10	DIN-15 Mounting rail
inch:	5.1	5.1	3.0	MIV 10	DIN-35 Mounting rail
Materials:				FP A 125/130	Front plate (Aluminium)
<b>Material:</b>	Polycarbonate			HFP 130	Front plate hinge series
<b>Base colour:</b>	RAL 7035 -light grey			FP 22046	Wall fastening lug (4 pcs)
<b>Cover screws material:</b>	Polyamide			Rating:	
<b>Cover colour:</b>	RAL 7035 -light grey			Ingress Protection (EN 60529): IP66/IP67	
<b>Cover screws colour:</b>	Grey			Impact Resistance (EN 62262): IK08	
<b>Gasket material:</b>	TPE			Electrical insulation: Totally insulated	
Temperatures:				Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperature °C (short term):</b>	-40 ... 120 °C			UV resistance: UL 508	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Flammability Rating: UL 746C 5"	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			NEMA Class: NEMA 1, 4, 4X, 6	
Accessories:				Certificates:	
MIV 125	Mounting plate (Galvanized steel)			Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

