

Lytebeam - 3-Circuit Track - Standard Unit

Lytebeam 3-circuit - Standard Track - 2m - Silver
2037841



Product features

- Lytebeam 3 Circuit deep beam profile, direct and indirect channels, rear beam section may be used to carry other electrical services, extruded aluminium body, suitable for suspending, (LxWxH) 2000x42x94mm, 5.00kg, Silver RAL 9006, Class 1, maximum installed load: 3x3680W (11040W), fuse: 3x16A, supply cable: 5 x 1.5mm², 400 VAC supply



PRODUCT OVERVIEW

Product name	Lytebeam 3-circuit - Standard Track - 2m - Silver
Technology	Accessory
Housing	Aluminium
Mount	Suspended
Environment	Internal
General application	Museums & Galleries
ETIM Class	EC000101
Warranty	5 years
Housing colour	Silver
Product EAN number	5025768378418

DATA TABLE

General data

Product name	Lytebeam 3-circuit - Standard Track - 2m - Silver
Technology	Accessory
Housing	Aluminium
Mount	Suspended
Environment	Internal
General application	Museums & Galleries
ETIM Class	EC000101
Warranty	5 years

Optical data

Adjustable chromaticity	N
-------------------------	---

Electrical data

Transformer required	Yes
----------------------	-----

Physical data

Housing colour	Silver
Nominal Product Length (mm)	2000
Nominal Product Width (mm)	42
Nominal Product Height (mm)	94

Lytebeam - 3-Circuit Track - Standard Unit

Lytebeam 3-circuit - Standard Track - 2m - Silver
2037841

Weight (kg)	5.0
-------------	-----

Packaging

Single packaging type	Carton
Product EAN number	5025768378418
Packaging single length / height (cm)	205.0
Packaging single width (cm)	10.0
Packaging single depth (cm)	5.0
Units per outer package	1
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	10.0
Packaging outer depth (cm)	5.0

TECHNICAL DRAWINGS

