


Mini Continuum II - Direct - Trimless - Extensions

MC2 0.6M 3K DALI WHT OPAL

2093159



Product features

- 2093159 MC2 0.6M 3K DALI WHT OPAL Continuous lines of LED light, white RAL 9016, direct distribution, extension module, trimless detail for a seamless finish, suitable for recessed, semi-recessed, surface-mounted or suspended installation either horizontally or vertically, various accessories available, compact and minimalist design based on the Golden Mean, ideal for offices, meeting rooms, corridors, education facilities, museums and libraries, extruded aluminium body, diffuser: opal, colour temperature: 3000K warm white, total system power: 10W, total fixture output: 1100lm, luminaire efficacy: 110lm/W, LOR: 100%, colour rendering: Ra >80, LED Chromacity: 3 step MacAdam ellipse, lifespan: 66,000 hours L90B10, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 400mA, electronic driver, DALI dimmable, electrical protection: CLASS I, IP20, suitable for internal environment only.



PRODUCT OVERVIEW

Product name	MC2 0.6M 3K DALI WHT OPAL
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
E-number FI	4237846
Warranty	5 years
Fixture luminous flux (lm)	1100
Luminaire efficacy (lm/W)	110
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 17
Photobiological Risk Group	RG0
Total power consumption (W)	10
Electrical protection	Class I
Control gear type	Electronic ballast
Dimming method	DALI
Minimum dimming level (%)	1
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5025768931590

Mini Continuum II - Direct - Trimless - Extensions

MC2 0.6M 3K DALI WHT OPAL
2093159

DATA TABLE

General data

Product name	MC2 0.6M 3K DALI WHT OPAL
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Education, Hospitality, Office, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4237846
Warranty	5 years

Optical data

Fixture luminous flux (lm)	1100
Luminaire efficacy (lm/W)	110
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Glare control	< 17
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	10
Mains voltage (V)	220-240V
Lamp power factor	0.95
Electrical protection	Class I
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Drive current (mA)	400
Inrush Current (A)	17
Inrush Duration (µs)	170
Energy Efficiency Class (A->G) of contained light source	C
Max. Luminaires per 16A C Breaker	48

Lifetime data

Lifespan L70 B50	120000
Lifespan L80 B20	120000
Lifespan L90 B10	66000

Mini Continuum II - Direct - Trimless - Extensions

MC2 0.6M 3K DALI WHT OPAL
2093159



Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser finish	Opal
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	600
Nominal Product Width (mm)	54
Nominal Product Height (mm)	86
Cutout Dimensions (W x L in mm or Diameter in mm)	60 x 600
Weight (kg)	1.5
Recessed Depth (mm)	136

Packaging

Single packaging type	Carton
Product EAN number	5025768931590
Packaging single length / height (cm)	65.0
Packaging single width (cm)	9.0
Packaging single depth (cm)	10.0
DUN14 (outer)	05025768931590
Units per outer package	1
Packaging outer length / height (cm)	65.0
Packaging outer width (cm)	9.0
Packaging outer depth (cm)	10.0

PHOTOMETRY



TECHNICAL DRAWINGS

Mini Continuum II - Direct - Trimless - Extensions

MC2 0.6M 3K DALI WHT OPAL

2093159

