

Quarter circle milling cutter HSSE Co 5

Concave

ORION[®]

Application:

Quarter circle milling cutter for machining complex forms, e.g. bore radii in materials up to 1000 N/mm².

Execution:

- Finishing teeth
- 5° cutting angle
- Up to 5 mm radius - backed off radially and axially
- From 5.5 mm radius - ground chamfers
- Up to 8 mm radius - combination shank in accordance with DIN 1835 B and D
- From 8.5 mm radius - straight shank in accordance with DIN 1835 B
- For mounting in self-clamping chucks, e. g. Clarkson, Bahnmüller



Art. no.	15461 060
Brand	ORION
Manufacturer Part Number	15461060
Surface	Uncoated
Type	N
Number of cutting edges	4 PCS
Tool holding device	HB combined shank
Radius	6 mm
Min. cutting edge diameter	8 mm
Max. cutting edge diameter	20 mm
Length	67 mm
Shank diameter	16 mm
fz steel 700	0.02 mm
Gross Weight	0.100 kg
Product Group	106

EAN

4039247097142