

## Adjustable clamps

Angled



### Application:

For clamping workpieces.

### Execution:

- With support screw and clamping screw
- Made from heat-treated steel
- Painted

<b>Art. no.</b>	<b>26221 040</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	70292
<b>For table grooves according to DIN 650</b>	16 mm
<b>Suitable screw DIN 787</b>	M16 x 125 mm
<b>Min./max. clamping range</b>	13-48 mm
<b>Groove width</b>	18 mm
<b>Span iron length</b>	125 mm
<b>Span iron width</b>	50 mm
<b>Thread dimension</b>	M16
<b>Thread length</b>	55 mm
<b>Thickness</b>	25 mm
<b>Distance</b>	26 mm
<b>Length</b>	45 mm
<b>Gross Weight</b>	1.430 kg
<b>Product Group</b>	260



### EAN

4020772070298

