

## Fully extending drawer for HK cabinet/shelving system 800

Depth 700 mm

### Application:

For individual configuration of the HK cabinet housing/tool shelves. The drawers can be installed in the housing in any sequence, but the sum of the front heights must be equal to the useful height of the housing.

### Execution:

- Made of sheet steel with a reinforced, perforated bottom (25 mm hole grid)
- Run on Delrin rollers in rails which are suspended in the housing with plug caps
- Inner sides slotted all around, for attaching and fixing insert material such as compartment rails and dividers
- Equipped with aluminium handle strip, paper and cellon strips and lateral cover caps
- SOFT-CLOSE-AUTOMATIC for smooth and silent drawer closing, see no. 50392 005



<b>Art. no.</b>	<b>50315 366</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50315366
<b>Drawer front height</b>	120 mm
<b>Suitable for system</b>	800B
<b>Drawer cabinet height</b>	100 mm
<b>Mount height</b>	100 mm
<b>Drawer width (inner dimension)</b>	900 mm
<b>Drawer depth (inner dimension)</b>	700 mm
<b>Drawer surface</b>	0.63 m <sup>2</sup>
<b>Pullout type</b>	Full extension
<b>Load-carrying capacity</b>	200 kg
<b>Drawer with slots</b>	Yes
<b>Perforated drawer base</b>	Yes
<b>Material</b>	Sheet steel
<b>Colour of front</b>	Gentian blue RAL 5010
<b>Box colour</b>	Light grey RAL 7035
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	0.010 kg
<b>Product Group</b>	5BB

### EAN

4053625100903