

## Bolt cutters with coated tubular handles and plastic grip covers

Lever joint, high lever transmission

**ATORN**<sup>®</sup>

### Application

For cutting steel wires up to max. 44 HRC

### Version

- Interchangeable face mill
- Forged, robust blades with additional inductively hardened cutting edges, cutting hardness approx. 62 HRC
- Powerful elbow joint and impact-resistant, powder-coated steel tube handle
- ERGO grip sleeves make them comfortable to use
- Easy adjustment using double eccentric screws



<b>Art. No.</b>	<b>53230 046</b>
<b>Length</b>	460 mm
<b>Max. piano wire diameter cutting capacity</b>	5 mm
<b>Max. soft wire diameter cutting capacity</b>	8 mm
<b>Material of the grip handle</b>	1-component plastic

### EAN-Code

4050293681307