

Manual sweeping machine KM 70/20 C S2B

with 40 litre collection box

KÄRCHER

Application:

Ideal choice for cleaning small production facilities, car parks, shopping centres, schools, workshops, bus and railway stations as well as in outdoor areas of office buildings.

Version:

- with 2 side brushes
- metal drive on both sides for equally excellent sweeping performance when making left and right turns
- push handle foldable and adjustable in 3 different heights
- with dust filter for a clean exhaust air while sweeping
- Working width 480 mm, not including lateral brushes

Advantage:

- cleaning is up to 6 times faster than when using a normal broom.
- virtually maintenance-free: a simple mechanical construction. no motor and no battery.
- easy to control thanks to large wheels

Delivery:

main sweeping roller, 2 side brooms, folding handle



Art. no.	75730 151
Model	KM 70/20 C S2B
Max. working width	960 mm
Container capacity	42 l
Max. surface coverage per hour	3680 m ²
Length x width x height	1300 x 960 x 1050 mm
Weight	26 kg

EAN-Code

4039784718036