

VIP sling chains, quality class 10, 2-stranded

Cannot be shortened



Application:

For the safe and regulatory-compliant lifting of heavy loads.

Execution:

- CrNiMo stainless steel, special hardening and tempering, quality class 10
- Bright fluorescent pink powder coating (VIP)
- VIP-identification label with integrated chain test gauge, to check the three deposit criteria for sling chains (diameter wear, pitch extension and overload)
- VIP-Cobra-safety hook with patented wear marks showing the legal deposit maturity without measuring, marking points for check dimension of the jaw width
- Integrated heat indicator: in the event of inadmissible overheating above 400°C, the colour changes to jet black and small bubbles form
- 2 chain strands with fixed length

Advantage:

- Up to 30% higher carrying capacity compared to quality class 8 with the same nominal chain thickness
- No confusion with other quality classes
- Resistant to external mechanical wear and damage
- Longer service life

Delivery:

1-stranded or longer designs, stronger chain diameter, carrying capacities up to 56 t upon request.



Art. no.	77208 602
Brand	RUD
Manufacturer Part Number	25 101000016184
Stop chain design	2 threads
Chain, can be shortened	No
Effective length	1 m
Chain diameter	8 mm
Load-carrying capacity at 0-45° tilt angle	3500 kg
Load-carrying capacity at 45-60° tilt angle	2500 kg
EN standard	818-2
Colour	Pink
Gross Weight	6.280 kg
Product Group	775

