

## Ring bolt

Screwable sling point, 360° rotation

CARTEC

### Application:

For the safe attachment of loads.

### Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

### Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing



<b>Art. no.</b>	<b>77232 142</b>
<b>Brand</b>	CARTEC
<b>Manufacturer Part Number</b>	C807XHT42
<b>Design</b>	Without key
<b>Thread dimension</b>	M42
<b>Load-carrying capacity</b>	9 t
<b>Distance between lower edge of retainer holder and retainer</b>	118 mm
<b>Bracket width</b>	37 mm
<b>Bracket height</b>	38 mm
<b>Outer diameter</b>	158 mm
<b>Diameter 2</b>	110 mm
<b>Internal width</b>	82 mm
<b>Width of support plate</b>	87 mm
<b>Usable thread length</b>	65 mm
<b>Width across flats</b>	24 mm
<b>Weight</b>	5.7 kg
<b>Gross Weight</b>	5.700 kg
<b>Product Group</b>	775

### EAN

8013429916205