

Kabelentmantler Multi

- Universelles Abisolierwerkzeug für Koaxialkabel RG 59, RG 6, RG 7, RG 11
- Abisolieren der Außenummantelung von Koax-, UTP/STP-, Rund- und Flachkabeln
- flexibel einsetzbare Messerkassette 6mm (1/4")
- justierbare Abisolierklinge für Datenkabel
- zwei Abisolierklingen zum Abschneiden und Abmanteln von Telefon-Flachbandkabeln (4P/6P/8P) in einem Arbeitsgang
- integrierte Klinge zum Abschneiden von Datenkabeln
- inklusive Bürste zum Entflechten von Kabelschirmungen
- Gehäuse: Kunststoff, schlagfest



Art. No. 707-1660 SB

Dismantling Tool Multi

- Universal stripping tool for Coax cables RG 59, RG 6, RG 7, RG 11
- Strips outer coating of coaxial, UTP/STP, round and flat cables
- Includes interchangeable / reversible blade magazine 6mm (1/4")
- Adjustable stripping blade for data cables
- Two stripping blades for cutting and stripping flat telephone cables (4P/6P/8P) in one single operation
- Integrated blade for cutting data cables
- Uses black Velcro brush for folding back the braided shielding
- Housing: plastic, impact-resistant



Art. No.	Kapazität Capacity	Länge Length mm	Gewicht Weight g
707-1660 SB	RG 59, RG 6, RG 7, RG 11	125	100



Abisolieren von Rundkabel
Stripping of round cables



Abisolieren von Flachbandkabel
Stripping of flat cables

Koaxial-Kabelentmantler

- zum Abisolieren von Koaxial-Kabel RG 6, RG 58, RG 59
- Außenmantel, Abschirmung und Isolation werden in einem Arbeitsgang abisoliert
- Drehschnitt mit drei eingebauten Messern
- Schneidtiefe einstellbar mit Innensechskant-Schraubendreher (inklusive)
- der Messerabstand bleibt konstant
- Gehäuse: Kunststoff, schlagfest




Art. No. 707-1700 SB

Dismantling Tool for coaxial cables


- Strips coaxial cables RG 6, RG 58, RG 59
- For stripping outer coating, shielding and insulation in one operation
- Rotary cutting with three built-in blades
- Includes hex key to adjust blade depth
- Blade spacing remains constant
- Housing: plastic, impact-resistant



Art. No.	Kapazität Capacity	Länge Length mm	Gewicht Weight g
707-1700 SB	RG 6, RG 58, RG 59	110	50



Drehschnitt
Rotary cutting



einstellbare Schnitttiefe
Adjustable blade depth