


Panel Mount




FX0296/S

FX0296

- Protection Category PC1
- Fuse Size 5 x 20mm
- Screw Cap/Hand Release
- 6.3A, 250V



Fixing Details




3.2 MAX Panel
1.0 MIN Panel

Panel Mount




FX0296/1

- Protection Category PC1
- Fuse Size 5 x 20mm
- Screw Cap/Hand Release
- 6.3A, 250V



Fixing Details



3.2 MAX Panel
1.0 MIN Panel

| Specifications | FX0296, FX0296/S | FX0296/1 |
|-------------------------|---|---|
| Fuse Size: | 5 x 20mm | 5 x 20mm |
| Fuse Carrier: | FX0296 Screw cap/Hand release FX0296/S Screw cap/Screwdriver release | Screw cap/Hand release |
| Terminations: | Solder tags | Solder tags |
| Max. Rating: | 6.3A, 250V | 6.3A, 250V |
| Max. Power Dissipation: | 2.5W (@ 23°C) | 2.5W (@ 23°C) |
| Insulation Resistance: | >10 ⁸ MΩ @ 500V d.c. | >10 ⁸ MΩ @ 500V d.c. |
| A.C. Breakdown: | 2.5kV @ 50Hz | 2.5kV @ 50Hz |
| Contact Resistance: | <5mΩ | <5mΩ |
| Operating Temp: | -20°C to +85°C (ambient air temp + fuse temp rise) | -20°C to +85°C (ambient air temp + fuse temp rise) |
| Mouldings: | | |
| Body: | Glass Filled Nylon UL94V-0 rated Nylon | Glass Filled Nylon UL94V-0 rated Nylon |
| Cap: | UL94V-0 rated | UL94V-0 rated |
| Nut: | Glass Filled Nylon UL94V-0 rated | Glass Filled Nylon UL94V-0 rated |
| Contacts: | Brass, Silver or Tin Plated | Brass, Silver or Tin Plated |
| Accessories | P.No. 9820 (See page 205) | P.No. 9820 (See page 205) |
| RoHS | Compliant | Compliant |