

97

ZP25-3

Tools and harnessing machines



Manual tongs for termination of modular plugs, piercing technology, with ratchet, cutter and stripper

Range of application

Connector	P 126, P 127, P 128, P 303, P 303 S
Pole number	4P4C (RJ-10), 6P4C (RJ-14), 6P6C (RJ-12), 10P10C (RJ-48)
Pitch	1,02 mm
State of delivery of connectors	in bulk
Processable conductor	flat cable 1.02 mm

Features

Application	laboratory and sample production, harness repair
Stroke capacity	ca. 240/h

Dimensions and supply data

Dimensions (H x W x D)	70 mm x 200 mm x 30 mm
Weight	ca. 0,5 kg

97

ZP25-3

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
ZP25-3	-		1