




ESTGH080MSS00.5E08 (PG9)

Connection technology



1: O-ring

Product characteristics

Adapter plug

M12 connector

PG 9 - M12

Electrical data

Electrical design

AC/DC

Operating voltage [V]

50 V AC / 75 V DC

Environment

Ambient temperature [°C]

-25...85

Protection

IP 68

Mechanical data

Design

straight

Housing materials

diecast zinc nickel-plated

Weight [kg]

0.023

Electrical connection

Connection

PVC cable / 0.5 m;
8 x 0.25 mm² (14 x Ø 0.15 mm)

Wiring

Core colours

BN brown

BU blue

GN green


GY grey

PK pink

RD red

WH white

YE yellow



1 WH

2 BN

3 GN

4 YE

5 GY

6 PK

7 BU

8 RD

Colours to DIN 47100

Remarks

Pack quantity

[piece]

1