


## M12 ADAPTOR ON REAR OF MSUD VALVE PLUG FORM A 18MM


Form A (18 mm) – M12, connector at the rear  
without components  
3-pole

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration



*stay connected*

Product may differ from Image

**Approvals****Form**

41381

**Technical Data**

Operating voltage	110 V AC/DC
Operating current per contact	max. 4 A
Configuration	2 contacts + bridged PE
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	M3/M12 × 1 mm (recommended torque 0.4/0.6 Nm)

**General data**

Temperature range	-25...+85 °C
-------------------	--------------

**Commercial data**

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1