



Saddle Support Base T&B Catalog Number:


TC5141
78621087357
Active

UPC Number:
Status:
Description:

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 17.07mm (0.672 Inches), Width of 11.13mm (0.438 Inches), Height of 8.33mm (0.328 Inches), Mount with #6 Screw, 100 Pack

Features

This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.



General

Material	Nylon 6.6
Color	Natural
Mounting Method	Screw
Stud Size	#6 Pan head
Max Tie Width Accepted	.19
For Cable Ties	Up to 50 lbs.

Dimension Information

Length (inches)	.672
Width (inches)	.439

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 1000

Application Support

Material Selection Guide	Available on Website
--------------------------	----------------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com