




Pushing Performance

Han M23 P ComLock Hood 11-17 mm



Part number	09 15 600 0493
Specification	Han M23 P ComLock Hood 11-17 mm
HARTING eCatalogue	https://b2b.harting.com/09156000493

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M23 Power
Type of hood/housing	Hoods
Description of hood/housing	EMC version

Version

Locking type	ComLock rapid locking
Size	M23
Version	Top entry

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 in locked position
Clamping range	11 ... 17 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	5
Net weight	89.8 g
Country of origin	Germany
Customs tariff number	85366990