


NOTE:

1. The primary coating and secondary coating have the same color
2. RoHS 2011/65/EU and amendment directives (EU) 2015/863 compliant.
3. REACH 1907/2006/EC compliant.

Test:

Test Grade Designation:Each to Reference		
Grade IL/RL	standard	
Insertion Loss (IL)	≤0.3dB	IEC 61300-3-4
Return Loss(RL)	≥60dB	IEC 61300-3-6
Test Wavelength	1310nm	Single-Mode
End face inspection	×400	

1pc/SYNERGY 21 A bag/test report+label



MATERIAL LIST:

⑧	LC White Dust Cap	4 PCS	
⑦	LC/APC 8° Ferrule	4 PCS	
⑥	LC/APC 0.9 Green Connector	4 PCS	
⑤	LC 0.9 Green Boot	4 PCS	
④	Fiber Cable LOOSE TUBE SM 9/125 G657. A2 0.9mm YELLOW LSZH	Xm	
③	Fiber Cable LOOSE TUBE SM 9/125 G657. A2 0.9mm BLUE LSZH	Xm	
②	Fiber Cable LOOSE TUBE SM 9/125 G657. A2 0.9mm GREEN LSZH	Xm	
①	Fiber Cable LOOSE TUBE SM 9/125 G657. A2 0.9mm RED LSZH	Xm	

chart

ITEM NO.	LENGTH (m)
S215598V2	1.5

SYNERGY21

NO.	SPECIFICATION DESCRIPTION	QT' Y	REMARK	CUSTOMER	ITEM NO.
	NEW	2024-01-09	A	PRODUCT NAME Pigtail LC/APC 4 different colours	manufacture country: CHINA
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	UNIT mm
				DRAWNBY SYNERGY21	CHECKBY SYNERGY21
				APPOBY SYNERGY21	DATE 2024-01-09