

## Conical countersink, 90°, HSS, with bit holder

For universal use up to 1000 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

For countersinking, chamfering and deburring. For use in hand-held bit holders, electric hand drills and electric screwdrivers.

### Execution:

- profile-ground

### Advantage:

- Hexagonal shank, 1/4" provides a user-friendly tool chuck in the bit holder



<b>Art. no.</b>	<b>11492 205</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11492205
<b>Countersink angle</b>	90 Degree
<b>Cutting material</b>	HSS
<b>Surface</b>	Uncoated
<b>Number of cutting edges</b>	3 PCS
<b>Tool holding device</b>	1/4-inch hexagon shank
<b>Suitable for screw thread</b>	M10
<b>Spot-facer diameter</b>	20.5 mm
<b>Tip diameter</b>	3.5 mm
<b>Shaft length</b>	20 mm
<b>Length</b>	41 mm
<b>Gross Weight</b>	0.033 kg
<b>Product Group</b>	1EH

### EAN

4039247037100