

angular milling cutter 90° VSM490™-10 with shaft

for indexable milling inserts XN.U 1004..

WIDIA 

Application:

the WIDIA™ Victory™ angular milling cutter range VSM490™-10 or 15 has been specifically developed for higher cutting volumes and excellent surface qualities of plane surfaces and shoulders. the 90° angular milling cutters are suitable for a wide range of material applications – steel, cast iron, stainless steel and titanium – for machining ranging from roughing to finishing.

Execution:

- double-sided, robust indexable insert with four cutting edges
- highly positive geometry for lower cutting forces
- excellent surface quality on shoulder and front surface
- with internal cooling



Art. no.	16044 070
Brand	WIDIA
Manufacturer Part Number	6425512
Cutting edge diameter	25 mm
Clearance length	43 mm
Length	170 mm
Shank diameter	25 mm
max. ap	10 mm
Number of cutting edges	4 PCS
Gross Weight	0.320 kg
Product Group	1XJ

EAN

4059782478701