

## Electronic 3-point internal micrometer

Digimatic IP65

Mitutoyo

### Application:

For measuring through-bores and short centring shoulders in series production.

### Execution:

- LCD digit size 7.5 mm
- Titanium coated carbide
- Preset function
- Digimatic
- ABS function
- HOLD function
- Automatic switch-off after 20 min. Non-use
- Locking function

### Advantage:

- Long service life and high impact resistance

### Delivery:

Includes box, adjustment wrench, SR-44 battery, factory test certificate



<b>Art. no.</b>	<b>32017 689</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	468-161
<b>Min./max. length measuring range</b>	6-8 mm
<b>Data transmission type</b>	DIGIMATIC
<b>Digit increment</b>	0.001 mm
<b>Design</b>	Metric
<b>IP protection class</b>	IP 65
<b>Error limit</b>	0.002 mm
<b>Digit height</b>	7.5 mm
<b>Display</b>	Digital
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	1,5 V SR44
<b>Calibration Group</b>	I
<b>Gross Weight</b>	0.620 kg
<b>Product Group</b>	3MA

### EAN

4946368562827