

## Baby SharXS HTI 575 W/D5/56

Baby SharXS HTI | Metal halide lamps, double-ended



### Areas of application

- Concert and effect lighting

### Product family benefits

- Short 5 mm arc for high efficiency
- Overall length of 93 mm

### Product family features

- High efficiency thanks to short-arc technology
- High thermal load capacity thanks to eXtreme Seal (XS) technology - enables high pinch temperatures of up to 450 °C
- Hot restart capability
- Compact modular design - the same dimensions for all wattages within each SharXS family
- Pre-focus base for accurate lamp installation



# Product datasheet

## Technical data


### Electrical data

Nominal wattage	575.00 W
Nominal voltage	93.0 V
Lamp voltage	95 V
Ignition voltage	4.5 / 20 kVp
Nominal current	7.20 A
Lamp current	7.0 A

### Photometrical data

Nominal luminous flux	43000 lm
Luminance	50000 cd/cm <sup>2</sup>
Color temperature	5600 K
Color rendering index Ra	85
Luminous efficacy	75 lm/W

### Dimensions & weight



Diameter	16.0 mm
Length	93.0 mm
Light center length (LCL)	35.0 mm

### Temperatures & operating conditions

Maximum permitted pinch temperature	450 °C
-------------------------------------	--------

### Lifespan

Lifespan	500 h
----------	-------

### Additional product data

## Product datasheet

Base (standard designation)	SFc11-4
-----------------------------	---------

### Capabilities

Burning position	Any
------------------	-----

### Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	19-01-2022
Primary Article Identifier	4008321129345
Candidate List Substance 1	No declarable substances contained
Declaration No. in SCIP database	No declarable substances contained

### Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4008321129345	OSRHTI57580BY	-	-	-
4008321129352	OSRHTI57580BY	-	-	-
4008321674975	OSRHTI57580BY	-	-	-

## Product datasheet

---

### Safety advice

Because of their high luminance, UV radiation and high internal pressure during operation, Baby SharXS HTI lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Appropriate filters must ensure that UV radiation is reduced to an acceptable level. Mercury is released if the lamp breaks. Special safety precautions must be taken. Information on safety and handling is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321129345	Baby SharXS HTI 575 W/D5/56	Sleeve box 1	165 mm x 48 mm x 95 mm	0.75 dm <sup>3</sup>	150.60 g
4008321129352	Baby SharXS HTI 575 W/D5/56	Shipping carton box 10	- x - x -		
4008321674975	Baby SharXS HTI 575 W/D5/56	Shipping carton box 10	235 mm x 225 mm x 210 mm	11.10 dm <sup>3</sup>	

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.