

## Technical Data Sheet

### Description

Description	92 A/St
Part Number	10115188
Marking according to EN	A2 - P2
Conditions of use	<ul style="list-style-type: none"> <li>organic gases and vapors with a boiling point &gt; 65° C</li> <li>particles</li> </ul>



### Colour code

brown
white

### labels



### Characteristics

Weight [g]	260
Diameter [mm]	107
Height incl. thread [mm]	78
Connection	EN 148 - 1

### Breathing Resistance

at	EN 14387 requirements	Typical values
30 l / min	2,1 mbar	1,00 mbar
95 l / min	8,0 mbar	4,00 mbar

### Concentration of Testing Gases

Class 1	1000 ppm [0,1 Vol.-%]
Class 2	5000 ppm [0,5 Vol.-%]

### Performances

Filter type and class	Gases of reference	EN 14387 requirements	Typical values
A2	cyclohexane [C <sub>6</sub> H <sub>12</sub> ]	35 min	60 min
Filter type and class	Particles of reference	EN 143 requirements	Typical values
P2	sodium chloride [NaCl]	6.00%	< 0,50 %
	paraffin oil	6.00%	< 0,50%
R	Reusable according EN 143:2000/A1:2006		
D	Dolomite clogging test & marking according to EN 143:2000/A1:2006 and EN 14387		

### Material

Housing	aluminium
Cover (particle filter)	polypropylene
Filtering material	filtering paper / unimpregnated activated carbon

### Details/Special Information

Storage conditions & time	- 5 °C to + 50°C, < 90 % r. h. 6 years
---------------------------	--