

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

**MATERIAL**

Black-oxide steel, class 5.8 (tensile strength 500 N/mm<sup>2</sup>), hexagon socket head.

**STANDARD EXECUTIONS**


- **GN 913.3-KU** acetal resin based (POM) technopolymer bolt, natural colour.
- **GN 913.3-MS** brass bolt.

**FEATURES AND APPLICATIONS**

GN 913.3 grub screws, thanks to the brass or technopolymer bolt, prevent the contact surface from being damaged.

**SPECIAL EXECUTIONS ON REQUEST**

Different threadings and lengths.





**GN 913.3-KU**

Code	Description	d1	d3	l1	l3±0.3	sw	⚖
GN.13701	GN 913.3-M4-6-KU	M4	2	6	1	1.5	1
GN.13702	GN 913.3-M4-8-KU	M4	2	8	1	1.5	1
GN.13703	GN 913.3-M4-10-KU	M4	2	10	1	1.5	1
GN.13704	GN 913.3-M4-12-KU	M4	2	12	1	1.5	1
GN.13705	GN 913.3-M4-16-KU	M4	2	16	1	1.5	1
GN.13706	GN 913.3-M4-20-KU	M4	2	20	1	1.5	1
GN.13711	GN 913.3-M5-8-KU	M5	3	8	1	2.5	1
GN.13712	GN 913.3-M5-10-KU	M5	3	10	1	2.5	1
GN.13713	GN 913.3-M5-12-KU	M5	3	12	1	2.5	1
GN.13714	GN 913.3-M5-16-KU	M5	3	16	1	2.5	2
GN.13715	GN 913.3-M5-20-KU	M5	3	20	1	2.5	2
GN.13716	GN 913.3-M5-25-KU	M5	3	25	1	2.5	3
GN.13720	GN 913.3-M6-10-KU	M6	3.5	10	1.3	3	1
GN.13721	GN 913.3-M6-12-KU	M6	3.5	12	1.3	3	1
GN.13722	GN 913.3-M6-16-KU	M6	3.5	16	1.3	3	2
GN.13723	GN 913.3-M6-20-KU	M6	3.5	20	1.3	3	3
GN.13724	GN 913.3-M6-25-KU	M6	3.5	25	1.3	3	4
GN.13725	GN 913.3-M6-32-KU	M6	3.5	32	1.3	3	5
GN.13726	GN 913.3-M6-40-KU	M6	3.5	40	1.3	3	6
GN.13728	GN 913.3-M6-50-KU	M6	3.5	50	1.3	3	8


**GN 913.3-KU**

Code	Description	d1	d3	l1	l3±0.3	sw	⚖
GN.13729	GN 913.3-M8-12-KU	M8	5	12	1.6	4	2
GN.13730	GN 913.3-M8-16-KU	M8	5	16	1.6	4	4
GN.13731	GN 913.3-M8-20-KU	M8	5	20	1.6	4	5
GN.13732	GN 913.3-M8-25-KU	M8	5	25	1.6	4	7
GN.13733	GN 913.3-M8-32-KU	M8	5	32	1.6	4	9
GN.13734	GN 913.3-M8-40-KU	M8	5	40	1.6	4	11
GN.13736	GN 913.3-M8-50-KU	M8	5	50	1.6	4	14
GN.13738	GN 913.3-M8-63-KU	M8	5	63	1.6	4	18
GN.13739	GN 913.3-M10-16-KU	M10	6.5	16	1.9	5	5
GN.13740	GN 913.3-M10-20-KU	M10	6.5	20	1.9	5	7
GN.13741	GN 913.3-M10-25-KU	M10	6.5	25	1.9	5	9
GN.13742	GN 913.3-M10-32-KU	M10	6.5	32	1.9	5	13
GN.13743	GN 913.3-M10-40-KU	M10	6.5	40	1.9	5	16
GN.13744	GN 913.3-M10-50-KU	M10	6.5	50	1.9	5	21
GN.13746	GN 913.3-M10-63-KU	M10	6.5	63	1.9	5	28
GN.13748	GN 913.3-M10-80-KU	M10	6.5	80	1.9	5	36
GN.13749	GN 913.3-M12-20-KU	M12	8	20	2.1	6	9
GN.13750	GN 913.3-M12-25-KU	M12	8	25	2.1	6	13
GN.13751	GN 913.3-M12-32-KU	M12	8	32	2.1	6	18
GN.13752	GN 913.3-M12-40-KU	M12	8	40	2.1	6	24
GN.13753	GN 913.3-M12-50-KU	M12	8	50	2.1	6	31
GN.13754	GN 913.3-M12-63-KU	M12	8	63	2.1	6	40
GN.13756	GN 913.3-M12-80-KU	M12	8	80	2.1	6	52
GN.13758	GN 913.3-M12-100-KU	M12	8	100	2.1	6	66

**GN 913.3-MS**

Code	Description	d1	d2	l1	l2	sw	
GN.13801	GN 913.3-M4-6-MS	M4	2.5	6	0.5	2	1
GN.13802	GN 913.3-M4-8-MS	M4	2.5	8	0.5	2	1
GN.13803	GN 913.3-M4-10-MS	M4	2.5	10	0.5	2	1
GN.13804	GN 913.3-M4-12-MS	M4	2.5	12	0.5	2	1
GN.13805	GN 913.3-M4-16-MS	M4	2.5	16	0.5	2	1
GN.13806	GN 913.3-M4-20-MS	M4	2.5	20	0.5	2	1
GN.13811	GN 913.3-M5-8-MS	M5	3	8	0.5	2.5	1
GN.13812	GN 913.3-M5-10-MS	M5	3	10	0.5	2.5	1
GN.13813	GN 913.3-M5-12-MS	M5	3	12	0.5	2.5	1
GN.13814	GN 913.3-M5-16-MS	M5	3	16	0.5	2.5	2
GN.13815	GN 913.3-M5-20-MS	M5	3	20	0.5	2.5	2
GN.13816	GN 913.3-M5-25-MS	M5	3	25	0.5	2.5	3
GN.13821	GN 913.3-M6-10-MS	M6	4	10	1	3	1
GN.13822	GN 913.3-M6-12-MS	M6	4	12	1	3	2
GN.13823	GN 913.3-M6-16-MS	M6	4	16	1	3	2
GN.13824	GN 913.3-M6-20-MS	M6	4	20	1	3	3
GN.13825	GN 913.3-M6-25-MS	M6	4	25	1	3	4
GN.13826	GN 913.3-M6-32-MS	M6	4	32	1	3	5
GN.13827	GN 913.3-M6-40-MS	M6	4	40	1	3	6
GN.13828	GN 913.3-M6-50-MS	M6	4	50	1	3	8

**GN 913.3-MS**

Code	Description	d1	d2	l1	l2	sw	
GN.13831	GN 913.3-M8-12-MS	M8	6	12	1.5	4	3
GN.13832	GN 913.3-M8-16-MS	M8	6	16	1.5	4	5
GN.13833	GN 913.3-M8-20-MS	M8	6	20	1.5	4	6
GN.13834	GN 913.3-M8-25-MS	M8	6	25	1.5	4	7
GN.13835	GN 913.3-M8-32-MS	M8	6	32	1.5	4	10
GN.13836	GN 913.3-M8-40-MS	M8	6	40	1.5	4	12
GN.13837	GN 913.3-M8-50-MS	M8	6	50	1.5	4	15
GN.13838	GN 913.3-M8-63-MS	M8	6	63	1.5	4	19
GN.13841	GN 913.3-M10-16-MS	M10	8	16	2	5	7
GN.13842	GN 913.3-M10-20-MS	M10	8	20	2	5	9
GN.13843	GN 913.3-M10-25-MS	M10	8	25	2	5	11
GN.13844	GN 913.3-M10-32-MS	M10	8	32	2	5	15
GN.13845	GN 913.3-M10-40-MS	M10	8	40	2	5	18
GN.13846	GN 913.3-M10-50-MS	M10	8	50	2	5	23
GN.13847	GN 913.3-M10-63-MS	M10	8	63	2	5	30
GN.13848	GN 913.3-M10-80-MS	M10	8	80	2	5	38
GN.13851	GN 913.3-M12-20-MS	M12	10	20	2	6	12
GN.13852	GN 913.3-M12-25-MS	M12	10	25	2	6	16
GN.13853	GN 913.3-M12-32-MS	M12	10	32	2	6	21
GN.13854	GN 913.3-M12-40-MS	M12	10	40	2	6	27
GN.13855	GN 913.3-M12-50-MS	M12	10	50	2	6	34
GN.13856	GN 913.3-M12-63-MS	M12	10	63	2	6	43
GN.13857	GN 913.3-M12-80-MS	M12	10	80	2	6	56
GN.13858	GN 913.3-M12-100-MS	M12	10	100	2	6	70

