

Product Name: 4 Zones Rainbow Remote (2.4GHz) Model No.: S2W+

Product Parameters

Working Voltage: 3V(AAA battery*2PCS)


Transmitting Power: 6dBm

Standby Power: 20µA

RF: 2.4GHz Modulation Method: GFSK


Control Distance: 30m

Φ70mm 24mm





1PC/BOX

G.W.: 0.076KGS



colors to choose





Adopt 2.4G wireless transmitting technology, with strong anti-interference,

long distance transmission; Control distance 30m; easier operation



LED Controller

Downlight

Magnetic Light

10000000000

Brightness / •

Saturation

All zone



Smart Switch

RGB / Color temp.

Turn off lights

4 Zones

Rail Tracklight



Touch Ring: Brightness, saturation, color temperature, RGB use together. (It turns to adjust brightness by default if remote is not operated for 3 seconds)

Low power consumption, longer usage time

2 AAA Battery for power supply

