

SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE


110V/230V LED+RC PG9

Form A (18 mm)
110/230 V AC/DC with LED and RC
PG 9



Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



stay connected



Height: 41 mm

Product may differ from Image

Approvals



Form

29141

Technical Data

Operating voltage	110 V AC/DC $\pm 10\%$ and 230 V AC/DC $\pm 10\%$
Operating current per contact	max. 1 A
Max. power (W)	max. 50 W(VA)
Connection cross section	4 mm ² single core, with ferrule end 1.5 mm ²
Sealing range (cable diameter)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	PG 9; (PG11, NPT 1/2" on request)
Protection	IP65 inserted and tightened (EN 60529), with gland

General data

Temperature range	-20...+60 °C
-------------------	--------------

Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1